

# PSI Phoenix Scientific Industries



High performance process solutions

## HERMIGA 120/50 V3I ATOMISER

The HERMIGA 120/50 V3I is a high performance atomiser using PSI's close-coupled die technology; accordingly fine powder production down to 10 microns median with rapid solidification rates in the region of  $10^5$  to  $10^6$  Ksec<sup>-1</sup> are possible.

As a result of the continuous development program the HERMIGA 120/50 benefits from PSI's unique geometry die design allowing consistent and reproducible production of high quality spherical metal powders.

A wide range of options is available in order to produce the system that best suits your requirements.

- Gas rack system available to enable processing using various gases such as;
  - Argon
  - Helium
  - Nitrogen
- Melting capacity is 50 kg of steel or equivalent volumes of other alloys.
- Control system includes sophisticated data logging facility
- Options available include;
  - Oxygen monitoring
  - Optical Pyrometry
  - Vacuum pump upgrades
  - Melt charging / sampling
  - Gas superheat, gas cooling
  - Particle injection system
  - Additional transfer hoppers

See overleaf



## HERMIGA 120/50 V2I

A capable, sophisticated and user friendly atomiser for the production of batch quantities of metal powder.

PSI Ltd - Apex Business Park - Hailsham - East Sussex BN27 3JU - United Kingdom

Phone: +44 (0)1323 449001 - Fax: +44 (0)1323 449002 - E-mail: [info@psiltd.co.uk](mailto:info@psiltd.co.uk) - [www.psiltd.co.uk](http://www.psiltd.co.uk)

# PSI



# Phoenix Scientific



# Industries

## High performance process solutions

## HERMIGA 120/50 V3I ATOMISER

### Typical system data

Furnace Type:	Induction heated tilt and pour furnace
Tundish Type:	Induction heated tundish to ensure good temperature control
Melt Capacity:	50 kg steel or equivalent volume of other alloys
Atomisation Die Type:	Supersonic invariable type 'close-coupled' die
Atomisation Rate:	Typically 3—6 kg/minute of steel
Typical Median ( $d_{50}$ ):	In range 10 to 100 $\mu\text{m}$
Atomisation Chamber:	Water cooled, dual section 304L stainless steel
Powder Handling:	High efficiency cyclone, partial and HEPA filters
Gas Requirement:	Argon/Nitrogen/Helium max 6kg/min. Min pressure 30 bar.
Systems Size (L x D x H):	Dimensions of 10.0 m x 6.5 m x 7.5 m
System Weight:	Approx. 25 Tonnes



PSI Ltd - Apex Business Park - Hailsham - East Sussex BN27 3JU - United Kingdom

Phone: +44 (0) 1323 449001 - Fax: +44 (0) 1323 449002 - E-mail: [info@psiltd.co.uk](mailto:info@psiltd.co.uk) - [www.psiltd.co.uk](http://www.psiltd.co.uk)